



# CorePro LED tube Mains T5

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Product Length	1,200 mm
Bulb Shape	T5
Net Weight (Piece)	0.124 kg

## Approval and Application

Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C


## Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

## Product Data


Order product name	CorePro LEDtube 1200mm 16W830 G5 I APR
Full product name	CorePro LEDtube 1200mm 16W830 G5 I APR
Full product code	871869673202100
Order code	73202100
Material Nr. (12NC)	929001380908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696732021
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696732038

## Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 16W830 G5 I APR	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm

## Photometric data




Light Distribution Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR



Spectral Power Distribution Colour - CorePro LEDtube 1200mm 16W830 G5 I APR

# CorePro LED tube Mains T5


## Photometric data




© 2023 Philips Lighting B.V. Page 11

General uniform lighting - CorePro LEDtube 1200mm 16W830 G5 I APR


## Lifetime




ESSENTIAL LEDtube 8-16W G5 830-865 APR



ESSENTIAL LEDtube 8-16W G5 830-865 APR




ESSENTIAL LEDtube 8-16W G5 830-865 APR



Lumen Maintenance Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR

# CorePro LED tube Mains T5

## Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 1200mm 16W830 G5 I APR

