



Classic filament LED bulbs

LED classic 60W G93 E27 WW CL ND RF 1PF4

CorePro, LEDbulb, G95, 60 W, E27, 2700 K, 806 lm, CRI 80, 15000 hour(s), Glass

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information		LLMF At End Of Nominal Lifetime (Nom)	
Cap-Base	E27		70 %
Nominal lifetime	15,000 hour(s)	Operating and Electrical	
Switching Cycle	20,000	Line Frequency	50 to 60 Hz
Rated Lifetime (Hours)	15,000 hour(s)	Input Frequency	50 to 60 Hz
Lighting Technology	LEDbulb	Power Consumption	7 W
Flux measurement reference	Sphere	Lamp Current (Nom)	60 mA
Light Technical		Wattage Equivalent	60 W
Color Code	827 [CCT of 2700K]	Starting Time (Nom)	0.5 s
Beam Angle (Nom)	300 degree(s)	Warm-up time to 60% light	0.5 s
Luminous Flux	806 lm	Power Factor (Fraction)	0.51
Color Designation	Warm White (WW)	Voltage (Nom)	220-240 V
Correlated Color Temperature (Nom)	2700 K	Temperature	
Luminous Efficacy (rated) (Nom)	115.00 lm/W	T-Case Maximum (Nom)	45 °C
Color Consistency	<6		
Color rendering index (CRI)	80		

Classic filament LED bulbs

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Overall length	140 mm
Overall width	95 mm
Overall height	140 mm
Dimensions (Height x Width x Depth)	140 x 95 x 140 mm
Bulb Shape	G95
Net Weight (Piece)	0.060 kg

Approval and Application

Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	1825194
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data

Order product name	LED classic 60W G93 E27 WW CL ND RF 1PF4
Full product name	LED classic 60W G93 E27 WW CL ND RF 1PF4
Full product code	871869674245700
Order code	929001387901
Material Nr. (12NC)	929001387901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696742457
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696742464



Dimensional drawing



Product	D	C
LED classic 60W G93 E27 WW CL ND RF 1PF4	95 mm	140 mm


Classic filament LED bulbs

Photometric data




General uniform lighting - LED classic 60W G95 E27 WW CL ND 1PF

Spectral Power Distribution Colour - LED classic 60W G95 E27 WW CL ND 1PF




Light Distribution Diagram - LED classic 60W G95 E27 WW CL ND 1PF

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED classic 60W G95 E27 WW CL ND 1PF

Classic filament LED bulbs

