Australia and New Zealand Certificate of Conformity/Approval-addendum

Certificate
ULL-103776-A1

Issue date
2026-06-10

Expiration date
2030-03-06

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic Controlgear for LED Modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

Certificate of Conformity issued under Queensland Government's Recognised External Certification Scheme (RECS)
Certificate of Approval issued under NSW Government's Recognised External Approval Scheme (REAS)
ANZ Certification Scheme requirements.

Amarjit Singh (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Conformity/Approval-addendum

Certificate No: ULL-103776-A1
Original Date of Certification: 2025-03-06
Date of Issue/Revision: 2026-06-10

Trade Name or Trademark: PHILIPS, SIGNIFY, ADVANCE, XITANIUM

Risk Class / NSW Declared Class: LEVEL 3 - Power Supply or Charger : Power Supply for Lighting Purposes - Electronic - LED Driver

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM mark must be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled
The product approval mark ULL-103776-EA shall be placed on declared articles offered for sale in New South Wales and New Zealand

Additional Certification Conditions: None.

Model Details:

Model Name	Marked Input Voltage	Marked Input Frequency	Marked Input Current	Marked Input Power	Marked Output Voltage	Marked Output Current	Marked Output Power
9290014207	220-240 Vac	50/60 Hz	0.023 Aac	5.25 W	29-40 Vdc, 60 Vdc max.	0.1 Adc	4 W
9290014208	220-240 Vac	50/60 Hz	0.033 Aac	7.4 W	29-40 Vdc, 60 Vdc max.	0.15 Adc	6 W
9290014209	220-240 Vac	50/60 Hz	0.04 Aac	9 W	8-20 Vdc, 60 Vdc max.	0.35 Adc	7 W
9290014210	220-240 Vac	50/60 Hz	0.044 Aac	9.8 W	29-40 Vdc, 60 Vdc max.	0.2 Adc	8 W
9290014211	220-240 Vac	50/60 Hz	0.052 Aac	12 W	29-40 Vdc, 60 Vdc max.	0.25 Adc	10 W
9290014212	220-240 Vac	50/60 Hz	0.056 Aac	12.8 W	8-20 Vdc, 60 Vdc max.	0.5 Adc	10 W
9290014213	220-240 Vac	50/60 Hz	0.072 Aac	16 W	29-40 Vdc, 60 Vdc max.	0.35 Adc	14 W
9290014214	220-240 Vac	50/60 Hz	0.08 Aac	18 W	8-20 Vdc, 60 Vdc max.	0.75 Adc	15 W

Additional Information:

Additional rating information: IC, Independent, SELV.
Details of addendum :
- Trade names “SIGNIFY”, “XITANIUM”, and “ADVANCE” added.

The WorkSafe NZ test report acceptance conditions outlined in NZ Gazette notices 2022-au3179 and 2022-au3180 have been verified.

© 2026 UL LLC. All rights reserved.