中国国家强制性产品认证证书

证书编号：2019011002165417

认证委托人名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交直流电子控制装置（内装式（II 类），恒流模式，EL，安全特低电压，ta：50℃，tc：80℃，定温热保护：110℃）
XITANIUM 20W/m 0.15-0.5A 52V 230V　输出：20W 0.5A Uout=60Vdc，
XITANIUM 20W/m 0.15-0.5A 54V 230V　输出：20W 0.5A Uout=60Vdc；输入：220-240V 50/60Hz，220-240VDC

产品标准和技术要求

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023

上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2026 年 04 月 02 日　**有效期至：**2029 年 03 月 03 日

本证书为变更证书，证书首次颁发日期：2019 年 03 月 21 日
证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

经中国合格评定国家认可委员会认可 CNAS C001-P

签发：

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019011002165417

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME,MODEL AND SPECIFICATION

A.C. or D.C. Supplied Electronic Controlgear for LED Modules (Built-in Class Ⅱ, Constant Current Mode, EL, SELV, ta:50℃, tc:80℃, Temperature Declared Thermally Protected:110℃)
XITANIUM 20W/m 0.15-0.5A 52V 230V Output: 20W 0.5A Uout=60Vdc, XITANIUM 20W/m 0.15-0.5A 54V 230V Output: 20W 0.5A Uout=60Vdc; Input: 220-240V 50/60Hz, 220-240VDC

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023
This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Apr.02,2026 **Valid until:** Mar.03,2029

Date of original issued: Mar.21,2019

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

SIGNATURE:

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.