



产品认证证书

证书编号: CQC19010222149

申请人名称及地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

制造商名称及地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产企业名称及地址

昕诺飞电子(厦门)有限公司(V012385)
厦门市云顶北路2000号

产品名称和系列、规格、型号

灯具用电源导轨系统(接合器, II类, IP20, t_a : 35°C, t_c : 85°C, SELV, 适宜直接安装在普通可燃材料表面)

见附件; 220-240V~ 50/60Hz, F_{max} : 50N, U_{out} : 60VdcMAX。

产品标准和技术要求

GB/T13961-2008; GB7000.1-2015

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-465431-2018 认证规则的要求, 特发此证。

发证日期: 2019年06月27日

本证书的有效性依据发证机构的定期监督获得保持。

主任:

陆楠



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0149809



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC19010222149

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE FACTORY

Signify Electronics (Xiamen) Co., Ltd. (V012385)
No.2000 North Yunding Road, Xiamen, Fujian Province, P.R. China

PRODUCT NAME, MODEL AND SPECIFICATION

Electrical Supply Track Systems For Luminaires (Track Adapter, Class II, IP20, ta: 35°C, tc: 85°C, SELV, Suitable For Direct Mounting On Normally Flammable Material)
See Appendix; 220-240V~ 50/60Hz, Fmax: 50N, Uout: 60VdcMAX.

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T13961-2008;GB7000.1-2015

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-465431-2018.

Valid from: Jun.27,2019

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

C 0149809



产品认证证书

附 录

证书编号: CQC19010222149

第 1 页 共 1 页

纸 号: 149809

Xitanium 42W/a 0.9/1.05A 40V 3CG 230V; Xitanium 42W/a 0.9/1.05A 40V 3CB 230V;
Xitanium 42W/a 0.9/1.05A 40V 3CW 230V; Xitanium 32W/a 0.7/0.8A 40V 3CG 230V;
Xitanium 32W/a 0.7/0.8A 40V 3CB 230V; Xitanium 32W/a 0.7/0.8A 40V 3CW 230V;
Xitanium 30W/a 0.6/0.75A 40V 3CG 230V; Xitanium 30W/a 0.6/0.75A 40V 3CB 230V;
Xitanium 30W/a 0.6/0.75A 40V 3CW 230V; Xitanium 20W/a 0.35/0.5A 40V 3CG 230V;
Xitanium 20W/a 0.35/0.5A 40V 3CB 230V; Xitanium 20W/a 0.35/0.5A 40V 3CW 230V;
Xitanium 10W/a 0.2/0.25A 40V 3CG 230V; Xitanium 10W/a 0.2/0.25A 40V 3CB 230V;
Xitanium 10W/a 0.2/0.25A 40V 3CW 230V;
以上均为: 220-240V~ 50/60Hz Fmax:50N Uout:60VdcMAX。

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>