



EU Declaration of Conformity

Document No.: 2021A0242

Year in which CE Mark was first affixed: 2019

1. Product Range / Model:

Product Range / Model:

NAME: LED driver

DESCRIPTION: See Annex

2. Manufacturer Name & Address:

Signify

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

3. This declaration of conformity is issued under the sole responsibility of the manufacturer.

4. Object of the declaration:

Product Code:

The Unique product ID number of all products under the family described above, please refer to the Annex: Specification of the products

5&6. The object of the declaration described above is in conformity with the following relevant Union harmonization legislation and with the applicable requirements of the following harmonized standards:

Low Voltage Directive (LVD), 2014/35/EU

- EN 61347-1:2015
- EN 61347-2-13:2014 + A1:2017

Electromagnetic compatibility Directive (EMC), 2014/30/EU

- EN IEC 55015:2019 + A11:2020
- EN 61547:2009
- EN IEC 61000-3-2:2019 + A1:2021
- EN 61000-3-3:2013 + A1:2019

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- Commission Regulation (EU) 2019/2020 and amendment Commission Regulation (EU) 2021/341

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN IEC 63000:2018

7. Additional information: The product in this declaration is produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Signed for and on behalf of:

2021-09-01, Eindhoven

Ms. C. Sweegers

Regulatory Affairs Manager

High Tech Campus 48

5656 AE Eindhoven, The Netherlands





EU Declaration of Conformity

Document No.: 2021A0242

Annex: Specification of the products:

12NC	10NC	Product Description	Brand	Remarks
929001475606	9290014756	Xitanium 10W/a 0.2/0.25A 40V 3CW 230V	PHILIPS	N/A
929001475680	9290014756	Xitanium 10W/a 0.2/0.25A 40V 3CW 230V	PHILIPS	N/A
929001476006	9290014760	Xitanium 10W/a 0.2/0.25A 40V 3CB 230V	PHILIPS	N/A
929001476406	9290014764	Xitanium 10W/a 0.2/0.25A 40V 3CG 230V	PHILIPS	N/A
929001476480	9290014764	Xitanium 10W/a 0.2/0.25A 40V 3CG 230V	PHILIPS	N/A
929001475706	9290014757	Xitanium 20W/a 0.35/0.5A 40V 3CW 230V	PHILIPS	N/A
929001475780	9290014757	Xitanium 20W/a 0.35/0.5A 40V 3CW 230V	PHILIPS	N/A
929001476106	9290014761	Xitanium 20W/a 0.35/0.5A 40V 3CB 230V	PHILIPS	N/A
929001476180	9290014761	Xitanium 20W/a 0.35/0.5A 40V 3CB 230V	PHILIPS	N/A
929001476506	9290014765	Xitanium 20W/a 0.35/0.5A 40V 3CG 230V	PHILIPS	N/A
929001476580	9290014765	Xitanium 20W/a 0.35/0.5A 40V 3CG 230V	PHILIPS	N/A
929001475806	9290014758	Xitanium 32W/a 0.7/0.8A 40V 3CW 230V	PHILIPS	N/A
929001475880	9290014758	Xitanium 32W/a 0.7/0.8A 40V 3CW 230V	PHILIPS	N/A
929001476206	9290014762	Xitanium 32W/a 0.7/0.8A 40V 3CB 230V	PHILIPS	N/A
929001476280	9290014762	Xitanium 32W/a 0.7/0.8A 40V 3CB 230V	PHILIPS	N/A
929001476606	9290014766	Xitanium 32W/a 0.7/0.8A 40V 3CG 230V	PHILIPS	N/A
929001476680	9290014766	Xitanium 32W/a 0.7/0.8A 40V 3CG 230V	PHILIPS	N/A
929001475906	9290014759	Xitanium 42W/a 0.9/1.05A 40V 3CW 230V	PHILIPS	N/A
929001475980	9290014759	Xitanium 42W/a 0.9/1.05A 40V 3CW 230V	PHILIPS	N/A
929001476306	9290014763	Xitanium 42W/a 0.9/1.05A 40V 3CB 230V	PHILIPS	N/A
929001476380	9290014763	Xitanium 42W/a 0.9/1.05A 40V 3CB 230V	PHILIPS	N/A
929001476706	9290014767	Xitanium 42W/a 0.9/1.05A 40V 3CG 230V	PHILIPS	N/A
929001476780	9290014767	Xitanium 42W/a 0.9/1.05A 40V 3CG 230V	PHILIPS	N/A
929002103606	9290021036	Xitanium 30W/a 0.6/0.75A 40V 3CW 230V	PHILIPS	N/A
929002103706	9290021037	Xitanium 30W/a 0.6/0.75A 40V 3CB 230V	PHILIPS	N/A
929002103806	9290021038	Xitanium 30W/a 0.6/0.75A 40V 3CG 230V	PHILIPS	N/A