Australia and New Zealand Certificate of Suitability

Certificate
ULL-104574

Issue date
2026-06-25

Expiration date
2031-06-25

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic driver for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104574
Date of Issue/Revision: 2026-06-25

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:

Xi LP 165W 0.5-1.5A S1 230V C170 sXt:
Uin: 220-240 V~, fn: 50/60 Hz, DC Iin: 0.82-0.74 A~, Pin: 178 W, PF: 0.95,
Uin: 186-250 VDC, Iin: 0.56 ADCmax,
Irated: 500-1500 mA, Prated: 165 W, Uoutput: 54-157 V, Uout=200 Vdc max,
ta: -40…+55 °C, tc: 85 °C, Built-in

Xi LP 165W 0.2-0.7A S1 230V C170 sXt:
Uin: 220-240 V~, fn: 50/60 Hz, DC Iin: 0.82-0.74 A~, Pin: 178 W, PF: 0.95,
Uin: 186-250 VDC, Iin: 0.56 ADCmax,
Irated: 200-700 mA, Prated: 165 W, Uoutput: 100-300 V, Uout=330 Vdc max,
ta: -40…+55 °C, tc: 85 °C, Built-in

Xi LP 165W 0.3-1.0A S1 230V C170 sXt:
Uin: 220-240 V~, fn: 50/60 Hz,DC Iin: 0.82-0.74 A~, Pin: 178 W, PF: 0.95,
Uin: 186-250 VDC, Iin: 0.56 ADCmax,
Irated: 300-1050 mA, Prated: 165 W, Uoutput: 80-235 V, Uout=300 Vdc max,
ta: -40…+55 °C, tc: 85 °C, Built-in

© 2026 UL LLC. All rights reserved.