中国国家强制性产品认证证书

证书编号：2019011002259859

认证委托人名称及地址

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产者名称及地址

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称及地址

产品名称和系列、型号、规格

LED模块用交直流电子控制装置（LED控制装置，独立式，恒流模式，安全特低电压，ta:55℃，tc:90℃，EL，II类，IP20，适宜直接安装在普通可燃材料表面，定温热保护：110℃，控制端口调光）
见附页；220-240V～ 50/60Hz， 186-250Vdc

产品标准和技术要求

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023

上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2025 年 12 月 17 日 **有效期至：**2029 年 12 月 10 日

本证书为变更证书，证书首次颁发日期：2019 年 12 月 16 日
证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

签发：谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019011002259859

NAME AND ADDRESS OF THE APPLICANT

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND ADDRESS OF THE MANUFACTURER

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME,MODEL AND SPECIFICATION

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Controlgear, Independent, Constant Current Mode, SELV, ta:55℃, tc:90℃, EL, Class Ⅱ, IP20, Suitable For Direct Mounting On Normally Flammable Material Surfaces, Temperature Declared Thermally Protected: 110℃, Controlled Port Dimming)

See Appendix；220-240V～ 50/60Hz， 186-250Vdc

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Dec.17,2025 **Valid until:** Dec.10,2029

Date of original issued: Dec.16,2019

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

SIGNATURE: 谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

中国国家强制性产品认证证书

证书编号：2019011002259859

证书附页：第 1 页 共 1 页

序号	型号	输入	输出电流（A）	最大工作电压（Vdc）	输出功率（W）
1	XITANIUM 50W WH 0.7-1.5A 54V TD/Is CL	220-240V ~ 50/60Hz，0.27A 186-250VDC，0.32A	1.5	60	50

本页为证书附页，应与证书主页同时使用。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司