



# 中国国家强制性产品认证证书

证书编号: 2023011002565109

发证日期: 2023 年 08 月 18 日  
有效期至: 2028 年 08 月 17 日

认证委托人名称 昕诺飞 (中国) 投资有限公司  
及注册地址 上海市闵行区田林路 888 弄 9 号楼

产品生产者名称 昕诺飞 (中国) 投资有限公司  
及注册地址 上海市闵行区田林路 888 弄 9 号楼

生产企业名称  
及生产地址

产品名称和系列、规格、型号 LED 模块用交流或直流电子控制装置 (LED 控制装置, 内装式, 自耦式, 恒流模式, 控制端口调光, ta:50°C, tc:75°C, 定温热保护: 110°C)  
见附件. 220-240V ~ 50/60Hz; 220-240VDC

产品标准和  
技术要求 GB 17625.1-2022;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。  
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。  
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2023011002565109

Valid from: Aug.18,2023

Valid until:Aug.17,2028


**NAME AND REGISTERED  
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.  
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED  
ADDRESS OF THE  
MANUFACTURER**

Signify (China) Investment Co., Ltd.  
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION  
OF THE FACTORY**



**PRODUCT MODEL(S)**

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Built-in, Auto-wound Controlgear,  
Constant Current Mode, Controlled Port Dimming, ta:50°C, tc:75°C, Temperature Declared Thermally  
Protected: 110°C)  
See Appendix. 220-240V ~ 50/60Hz; 220-240VDC

**STANDARDS AND  
TECHNICAL REQUIREMENTS**

GB 17625.1-2022;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





# 中国国家强制性产品认证证书

证书编号: 2023011002565109

第 1 页 / 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3258698

| 型号                                           | 输入                                                                                                                         | 输入电<br>流 (A) | 输出电压<br>(Vdc) | 最大输出电<br>压 (Vdc) | 输出电流<br>(A) | 输出功<br>率 (W) |
|----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|--------------|---------------|------------------|-------------|--------------|
| Xitanium 35W<br>0.08-0.35A<br>220V TD21 230V | 220-240V~<br>50/60Hz;<br>220-240V <br>39W | 0.18A        | 50-220VDC     | Max. 250VDC      | 0.08-0.35A  | 35W          |
| Xitanium 60W<br>0.08-0.35A<br>300V TD21 230V | 220-240V~<br>50/60Hz;<br>220-240V <br>66W | 0.30A        | 100-300VDC    | Max. 330VDC      | 0.08-0.35A  | 60W          |



中国质量认证中心

