



中国国家强制性产品认证证书

证书编号: 2020011002355163

发证日期: 2022年11月14日

有效期至: 2025年12月16日

认证委托人名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

产品生产者名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED 模块用交直流电子控制装置 (LED 控制装置, 内装式, 自耦式, 恒流模式, ta:50°C, tc:75°C, 定温热保护: 110°C, 不可调光)
见附件; 输入: 220-240V ~ 50/60Hz; 186-250Vdc

产品标准和技术要求 GB 17625.1-2012; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书, 证书首次颁发日期: 2020年12月16日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020011002355163

Valid from: Nov.14,2022

Valid until: Dec.16,2025

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND LOCATION
OF THE FACTORY**



PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Driver, Built-in, Auto-wound
Controlgear, Constant Current Mode, ta:50°C, tc:75°C, Temperature Declared Thermally Protected:
110°C, Non-Dimmable)
See Appendix; Input: 220-240V ~ 50/60Hz; 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Dec.16,2020

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦

CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

附 录

证书编号: 2020011002355163

第 1 页 共 1 页

纸 号: 3085291

序号	型号	输出电流(A)	输出电压 (Vdc)	最大输出电 压 (Vdc)	输出功率 (W)
1	Xitanium 35W 0.08-0.35A 220V IA21 230V	0.08-0.35	50-220	250	35
2	Xitanium 60W 0.15-0.5A 220V IA21 230V	0.15-0.5	50-220	250	60
3	Xitanium 35W 0.08-0.35A 220V MC21 230V	0.08-0.35	50-220	250	35
4	Xitanium 60W 0.15-0.5A 220V MC21 230V	0.15-0.5	50-220	250	60

输入: 220-240V~ 50/60Hz; 186-250Vdc

注: 此附录与证书同时使用时有效。



中国质量认证中心

