



中国国家强制性产品认证证书

证书编号: 2019011002252968

发证日期: 2022年10月17日

有效期至: 2024年11月26日

认证委托人名称
及注册地址 昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

产品生产者名称
及注册地址 昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、
规格、型号 LED 模块用交直流电子控制装置(LED 控制装置, 内装式, 恒流模式, 安全特低电压, ta:50°C, tc:75°C,
定温热保护: 110°C, 不可调光)
见附件; 输入: 220-240V~ 50/60Hz; 186-250Vdc

产品标准和
技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2019年11月26日

经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019011002252968

Valid from: Oct.17,2022

Valid until: Nov.26,2024

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**



PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Built-in, Constant Current Mode, SELV,
ta:50°C, tc:75°C, Temperature Declared Thermally Protected: 110°C, Non-Dimmable)
See Appendix; Input: 220-240V ~ 50/60Hz; 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Nov.26,2019

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号 2019011002252968

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3095655

序号	型号	输入	输出电流 (A)	输出电压 (Vdc)	最大输出电压 (Vdc)	输出功率
1	Xitanium 75W 0.7-2.0A 54V 230V	220-240V ~ 50/60Hz 0.38A	0.7-2.0	27-54	60Vdc	75W
		186-250Vdc 0.46-0.34A				
2	Xitanium 36W 0.3-1.0A 54V 230V	220-240V ~ 50/60Hz 0.2A	0.3-1.0	27-54	60Vdc	36W
		186-250Vdc 0.24-0.17A				



中国质量认证中心

