



# 中国国家强制性产品认证证书

证书编号: 2022011002508744

发证日期: 2022年11月09日

有效期至: 2027年11月08日

认证委托人名称 昕诺飞(中国)投资有限公司  
及注册地址 上海市闵行区田林路888弄9号楼

产品生产者名称 昕诺飞(中国)投资有限公司  
及注册地址 上海市闵行区田林路888弄9号楼

生产企业名称  
及生产地址

产品名称和系列、规格、型号 LED 模块用交直流电子控制装置(LED控制装置, 内装式, 自耦式, 恒流模式, 不可调光, ta:50°C, tc:75°C, 定温热保护: 110°C)  
见附件, 输入: 220-240V~ 50/60Hz, 186-250Vdc

产品标准和技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。  
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。  
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn) 查验证书信息



签发: 谢肇煦



中国质量认证中心





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2022011002508744

Valid from: Nov.09,2022

Valid until: Nov.08,2027


**NAME AND REGISTERED ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.  
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER**

Signify (China) Investment Co., Ltd.  
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION OF THE FACTORY**



**PRODUCT MODEL(S)**

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Driver, Built-in, Auto-wound Controlgear, Constant Current Mode, Non-dimmable, ta:50°C, tc:75°C, Temperature Declared Thermally Protected: 110°C)  
See appendix, Input: 220-240V ~ 50/60Hz , 186-250Vdc

**STANDARDS AND TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





# 中国国家强制性产品认证证书

证书编号 2022011002508744

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3083672

序号	型号	输入	输出电流 (A)	输出电压 (Vdc)	最大输出电压 (Vdc Max.)	输出功率 (W)
1	Xitanium 35W 0.08-0.35A 220V 21 230V	220-240V~, 50/60Hz, 0.18A; 186-250Vdc, 0.21-0.16A; 39W	0.08-0.35	50-220	250	35
2	Xitanium 60W 0.08-0.35A 300V 21 230V	220-240V~, 50/60Hz, 0.3A; 186-250Vdc, 0.36-0.27A; 66W	0.08-0.35	100-300	330	60
3	Xitanium 60W 0.15-0.5A 220V 21 230V	220-240V~, 50/60Hz, 0.31A; 186-250Vdc, 0.36-0.27A; 67W	0.15-0.5	50-220	250	60
4	Xitanium 90W 0.25-0.7A 220V 21 230V	220-240V~, 50/60Hz, 0.45A; 186-250Vdc, 0.53-0.39A; 97W	0.25-0.7	50-220	250	90
5	Xitanium 35W 0.08-0.35A 220V S21 230V	220-240V~, 50/60Hz, 0.18A; 186-250Vdc, 0.21-0.16A; 39W	0.08-0.35	50-220	250	35
6	Xitanium 60W 0.08-0.35A 300V S21 230V	220-240V~, 50/60Hz, 0.3A; 186-250Vdc, 0.36-0.27A; 66W	0.08-0.35	100-300	330	60
7	Xitanium 60W 0.15-0.5A 220V S21 230V	220-240V~, 50/60Hz, 0.31A; 186-250Vdc, 0.36-0.27A; 67W	0.15-0.5	50-220	250	60
8	Xitanium 90W 0.25-0.7A 220V S21 230V	220-240V~, 50/60Hz, 0.45A; 186-250Vdc, 0.53-0.39A; 97W	0.25-0.7	50-220	250	90



## 中国质量认证中心

