



中国国家强制性产品认证证书

证书编号: 2021011002366666

发证日期: 2022年12月16日

有效期至: 2026年02月03日

认证委托人名称
及注册地址 Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

产品生产者名称
及注册地址 Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称
及生产地址



产品名称和系列、规格、型号 LED 模块用交直流电子控制装置 (LED 控制装置, 内装式, 自耦式, 恒流模式, ta:50°C, tc:75°C, 定温热保护: 110°C, 控制端口调光)
见附件。220-240V ~ 50/60Hz; 186-250Vdc

产品标准和技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书, 证书首次颁发日期: 2021年02月03日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2021011002366666

Valid from: Dec.16,2022

Valid until: Feb.03,2026

NAME AND REGISTERED ADDRESS OF THE APPLICANT Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND LOCATION OF THE FACTORY [Redacted]

PRODUCT MODEL(S) A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Built-in, Auto-wound Controlgear, Constant Current Mode, ta:50°C, tc:75°C, Temperature Declared Thermally Protected: 110°C, Controlled Port Dimming)
See Appendix. 220-240V~ 50/60Hz; 186-250Vdc

STANDARDS AND TECHNICAL REQUIREMENTS GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Feb.03,2021

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号 2021011002366666

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3158156

序号	型号	输入	输出电流 (A)	输出电压 (Vdc)	最大输出电压 (Vdc)	输出功率 (W)
1	Xitanium 90W 0.25-0.7A 220V TD21 230V	220-240V ~ 50/60Hz 0.44A	0.25-0.70	50-220	250	90
		186-250Vdc 0.52A				
2	Xitanium 90W 0.25-0.7A 220V TD21 S 230V	220-240V ~ 50/60Hz 0.44A	0.25-0.70	50-220	250	90
		186-250Vdc 0.52A				
3	Xitanium 90W 0.15-0.5A 300V TD21 S 230V	220-240V ~ 50/60Hz 0.44A	0.15-0.50	100-300	330	90
		186-250Vdc 0.52A				
4	Xitanium 90W 0.15-0.5A 300V TD21CL 230V	220-240V ~ 50/60Hz 0.44A	0.15-0.50	100-300	330	90
		186-250Vdc 0.52A				



中国质量认证中心

