CERTIFICATE

Issued to:
Applicant:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, The Netherlands

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, The Netherlands

Product	:	Electronic controlgear for LED modules
Trade name(s)	:	PHILIPS
Type(s)/model(s)	:	Xitanium 300W 0.5-1.4A 300V iXt TD 230V

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:
- a type test according to the standard(s) EN 61347-2-13:2014, EN 61347-2-13:2014/A1:2017, EN 61347-1:2015, EN 61347-1:2015/A1:2021 and EN IEC 62384:2020
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 947556

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This certificate is issued on 13 December 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-126593

DEKRA Certification B.V.

B.T.M. Holtus
Managing Director

MT Tonsi
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL

PRODUCTS
RvA C 001

DEKRA Certification B.V. Meander 1051, 6825 MJ Arnhem P.O. Box 5185, 6802 ED Arnhem, The Netherlands
T +31 88 96 83000 F +31 88 96 83100 www.dekra-product-safety.com Company registration 09085396

SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	Electronic controlgear for LED modules
Trade name(s)	:	PHILIPS
Type(s)/model(s)	:	Xitanium 300W 0.5-1.4A 300V iXt TD 230V
Rated input voltage	:	220-240 Vac or 186-250 Vdc
Rated frequency	:	50/60 Hz at ac or DC
Input current	:	1,43 Aac or 1,69 Adc
Input power	:	315 W
Power factor	:	0,9C
Output curent	:	0,5-1,4 Adc
Output voltage	:	100-300 Vdc
Uout	:	330 V
Output power	:	300 W
Ambient temperature (ta)	:	-40…+60 °C
Max.case temperature (tc)	:	90°C
Description	:	built-in; EL

TESTS

Test requirements

EN 61347-2-13:2014
EN 61347-2-13:2014/A1:2017
EN 61347-1:2015
EN 61347-1:2015/A1:2021
EN IEC 62384:2020

Test result

The test results are laid down in DEKRA test file 614214600.

Additional information

Constant current type
No insulation between PRI and SEC

The tests were performed by the manufacturer under the conditions of the agreement concerning the manufacturer's right to conduct type tests for the ENEC certification system under supervision of DEKRA (CTF Stage 3).

The list of components is laid down in test report 6142146.50.

Conclusion

The examination proved that all requirements were met.

Factory locations

The factory locations are registered with the numbers 674666, 305810 and 1845.

Trade name(s) : PHILIPS stands for PHILIPS