Australia and New Zealand Certificate of Suitability

Certificate
ULL-104588

Issue date
2026-06-30

Expiration date
2031-06-30

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic controlgear for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104588
Date of Issue/Revision: 2026-06-30

Trade Name or Trademark: SIGNYFY, XITANIUM, PHILIPS, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Rating :
Xitanium 60W 0.15-0.5A 220V TD11 230V
Uin: 220-240 Vac, Iin: 0.30 Aac, fn: 50/60 Hz, DC,
Pin: 66 W, PF: 0.9C, Uin:186-250 Vdc, Iin: 0.36 Adc,
Irated: 0.15-0.5A, Prated: 60 W, Uoutput: 50-220 Vdc. Uout: 250 Vmax,
ta: -25…+50 °C, tc: 85 °C, Built-in,

Xitanium 35W 0.08-0.35A 220V TD11 230V:
Uin: 220-240 Vac, Iin: 0.18 Aac, fn: 50/60 Hz, DC,
Pin: 39 W, PF: 0.9C, Uin:186-250 Vdc, Iin: 0.21 Adc,
Irated: 0.08-0.35A, Prated: 35 W, Uoutput: 50-220 Vdc. Uout: 250 Vmax,
ta: -25…+60 °C, tc: 85 °C, Built-in,

© 2026 UL LLC. All rights reserved.