

MAS LEDtube Spectrum 1200mm 1500lm

929001826408



LEDtube, T8, Single-ended, 1200 mm, 100-277 V, 14 W, 36W TL-D, 2200 K, 1500 lm, 50000 hour(s)

LEDtube, T8, Single-ended, 1200 mm, 100-277 V, 14 W, LED alternative to 36W TL-D, 2200 K, 1500 lm, 50000 hour(s), 107 lm/W, G13, Beam angle 160 degree(s), 1200 mm, SDCM 6, PF 0.9, IP20

General Information

Cap-Base	G13
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LEDtube

Light Technical

Color Code	2200
Beam Angle (Nom)	160 degree(s)
Luminous Flux	1,500 lm
Color Designation	2200
Correlated Color Temperature (Nom)	2200 K
Luminous Efficacy (rated) (Nom)	107 lm/W
Color Consistency	<6
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Power Consumption	14 W
Lamp Current (Max)	150 mA
Lamp Current (Min)	55 mA
Wattage Equivalent	36 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	100-277 V
LED alternative to fluorescent lamp power	36W TL-D

Temperature

T-Case Maximum (Nom)	55 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Product Length	1,200 mm
Bulb Shape	T8
Net Weight (Piece)	0.245 kg


Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Dimensional drawing




Product Data


Order product name	MAS LEDtube Spectrum 1200mm 1500lm
Full product name	MAS LEDtube Spectrum 1200mm 1500lm
Full product code	871869678030500
Order code	929001826408
Material Nr. (12NC)	929001826408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696780305
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696780312

Product	D1	D2	A1	A2	A3
MAS LEDtube Spectrum 1200mm 1500lm	25.8 mm	28 mm	1,199.4 mm	1,206.5 mm	1,213.6 mm

Photometric data




Light Distribution Diagram - MAS LEDtube Spectrum 1200mm 1500lm




Spectral Power Distribution Colour - MAS LEDtube Spectrum 1200mm 1500lm


Lifetime




Life Expectancy Diagram




General uniform lighting - MAS LEDtube Spectrum 1200mm 1500lm




FailureRate



Lumen Maintenance Diagram - MAS LEDtube Spectrum
1200mm 1500lm



LifetimeVsTc



Lumen Maintenance Diagram - MAS LEDtube Spectrum
1200mm 1500lm

Related Documents

Documents and certificates	Document Name	Download
Environmental Product Declaration	Philips-MASTER-LEDtube-Mains-T8-COMF-7950860-Ref-929001826408-EPD.pdf	Download 