



專業 LEDtube

MAS LEDtube Spectrum 1200mm 1500lm

LEDtube, T8, 單端, 1200 mm, 100-277 V, 14 W, 36W TL-D, 2200 K, 1500 lm, 50000 h

LEDtube, T8, 單端, 1200 mm, 100-277 V, 14 W, LED alternative to 36W TL-D, 2200 K, 1500 lm, 50000 h, 107 lm/W, G13, 1200 mm, SDCM 6, PF 0.9, IP20

产品数据


一般資訊	
燈座基底	G13
標準使用壽命	50,000 h
切換週期	200,000
照明技術	LEDtube
照明技術	
色碼	2200
光束角 (Nom)	160 °
光通量	1,500 lm
色彩名稱	2200
相關色溫 (標稱)	2200 K
光效 (額定) (標準)	107 lm/W
色彩一致性	<6
演色性指數 (CRI)	-
標稱壽命末期流明維持率	70 %
運轉與電力	
輸入頻率	50 至 60 Hz
耗電量	14 W
燈具電流 (最大)	150 mA

燈具電流 (最小)	55 mA
相等瓦數	36 W
起始時間 (標稱)	0.5 s
達到 60% 光色的熱穩時間	0.5 s
功率因數 (比值)	0.9
電壓 (標稱)	100-277 V
日光燈具功率的 LED 替代選擇	36W TL-D
溫度	
T-case 上限 (標準)	55 °C
控制與調光	
可調光	否
機械與外罩	
產品長度	1,200 mm
燈泡形狀	T8
淨重 (個)	0.245 kg
認證與應用	
節能燈具產品	是

核准標記	符合 RoHS 標準 KEMA Keur 認證
符合歐盟 RoHS 標準	是
環境溫度範圍	-20 至 +45 °C
產品資料	
下訂產品名稱	MAS LEDtube Spectrum 1200mm 1500lm
完整產品名稱	MAS LEDtube Spectrum 1200mm 1500lm
完整產品代碼	871869678030500



訂單代碼	929001826408
材質 Nr. (12NC)	929001826408
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718696780305
分子 - 每一外盒包裝	10
EAN/UPC - 箱	8718696780312

二维绘图




Product	D1	D2	A1	A2	A3
MAS LEDtube Spectrum 1200mm 1500lm	25.8 mm	28 mm	1,199.4 mm	1,206.5 mm	1,213.6 mm

光度数据





Light Distribution Diagram - MAS LEDtube Spectrum 1200mm 1500lm

General uniform lighting - MAS LEDtube Spectrum 1200mm 1500lm




Spectral Power Distribution Colour - MAS LEDtube Spectrum 1200mm 1500lm


壽命



Life Expectancy Diagram




FailureRate



Lumen Maintenance Diagram - MAS LEDtube Spectrum 1200mm 1500lm

LifetimeVsTc



Lumen Maintenance Diagram - MAS LEDtube Spectrum 1200mm 1500lm

