PHILIPS

Lighting

Essential LED spot MR16

ESS LED MR16 3-35W 36D 830 SO 100-240V

LEDspot, MR16, 35 W, GU5.3, 3000 K, 230 lm, 15000 hour(s)

LEDspot, MR16, 35 W, GU5.3, 3000 K, 230 lm, 15000 hour(s), 76.00 lm/W

Product data

General Information	
Cap-Base	GU5.3
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	230 lm
Luminous Intensity (Nom)	550 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	76.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3 W
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	100-240 V

Temperature	
T-Case Maximum (Nom)	55 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	MR16
Net Weight (Piece)	0.040 kg

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	3 kWh
EU RoHS compliant	Yes

Essential LED spot MR16

Ambient temperature range	-20 to +40 °C

Application Conditions

Wireless Technology	Not applicable

Product Data

Order product name	ESS LED MR16 3-35W 36D 830 SO 100-240V
Full product name	ESS LED MR16 3-35W 36D 830 SO 100-240V
Full product code	871869680915000

Order code	929001874208
Material Nr. (12NC)	929001874208
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696809150
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696809167

Dimensional drawing



Product	D	C
ESS LED MR16 3-35W 36D 830 SO 100-240V	50.5 mm	46.5 mm

Photometric data



Accent Lighting Spots - ESS LED MR16 3-35W 36D 830 SO 100-240V



Spectral Power Distribution Colour - ESS LED MR16 3-35W 36D 830 SO 100-240V

Essential LED spot MR16

Photometric data



Light Distribution Diagram - ESS LED MR16 3-35W 36D 830 SO 100-240V

Lifetime



50W GU5-3 MR16



Lumen Maintenance Diagram - ESS LED MR16 3-35W 36D 830 SO 100-240V

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.