

Specialty Lamps

4A19/PER/YELLOW/G/E26/ND 4/1PF

LEDbulb, A19, 40 W, E26, 15000 hour(s), Glass

LEDbulb, A19, 40 W, E26, 15000 hour(s), Glass

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb

Light Technical	
Color Code	Yellow
Beam Angle (Nom)	330 degree(s)
Color Designation	Yellow
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	4 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.40

Voltage (Nom)	120 V
---------------	-------

Temperature	
T-Case Maximum (Nom)	125 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Yellow
Bulb Material	Glass
Overall length	106 mm
Overall width	60 mm
Overall height	106 mm
Dimensions (Height x Width x Depth)	106 x 60 x 106 mm
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.030 kg


Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	N/A

Specialty Lamps

LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C
Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	4A19/PER/YELLOW/G/E26/ND 4/1PF



Full product name	4A19/PER/YELLOW/G/E26/ND 4/1PF
Order code	929001937253
Material Nr. (12NC)	929001937253
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568856
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568851

Dimensional drawing



Product	D	C
4A19/PER/YELLOW/G/E26/ND 4/1PF	60 mm	106 mm

Photometric data




General uniform lighting - 4A19/PER/YELLOW/G/E26/ND 4/1PF

Light Distribution Diagram - 4A19/PER/YELLOW/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 4A19/PER/YELLOW/G/E26/ND 4/1PF

