

Classic filament LED bulbs

LEDClassic 35W ST64 E27 825 WV ND 2CT

LEDbulb, ST64, 35 W, E27, 2500 K, 400 lm, 15000 hour(s)

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Warranty period	1 years

Light Technical	
Color Code	825 [CCT of 2500K]
Beam Angle (Nom)	280 degree(s)
Luminous Flux	400 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2500 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	100-240 V

Temperature	
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Transparent amber

Classic filament LED bulbs

Bulb Shape	ST64
Net Weight (Piece)	0.056 kg

Approval and Application


EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	LEDClassic 35W ST64 E27 825 WV ND 2CT
--------------------	---------------------------------------



Full product name	LEDClassic 35W ST64 E27 825 WV ND 2CT
Order code	929001941648
Material Nr. (12NC)	929001941648
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	046677555986
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677555981

Dimensional drawing




Product	D	C
LEDClassic 35W ST64 E27 825 WV ND 2CT	64 mm	142 mm

Photometric data



Spectral Power Distribution Colour - LEDClassic 35W ST64 E27 825 WV ND 2CT


General uniform lighting - LEDClassic 35W ST64 E27 825 WV ND 2CT




Light Distribution Diagram - LEDClassic 35W ST64 E27 825 WV ND 2CT

Classic filament LED bulbs

Lifetime



LEDBulb E27 2500K



Lumen Maintenance Diagram - LEDClassic 35W ST64 E27 825 WV ND 2CT

