

Classic filament LED bulbs

8A19/PER/927-922/CL/G/E26/WGX 1FB T20

LEDbulb, A19, 60 W, E26, 2700 K, 2200 K, 800 lm, 15000 hour(s), Glass

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb

Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	800 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	85 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.75
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	60 °C

Classic filament LED bulbs

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Overall length	108 mm
Overall width	60 mm
Overall height	108 mm
Dimensions (Height x Width x Depth)	108 x 60 x 108 mm
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.030 kg

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes

LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data



Order product name	8A19/PER/927-922/CL/G/E26/WGX 1FB T20
Full product name	8A19/PER/927-922/CL/G/E26/WGX 1FB T20
Order code	929001969604
Material Nr. (12NC)	929001969604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677549497
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677549492

Dimensional drawing



Product	D	C
8A19/PER/927-922/CL/G/E26/WGX 1FB T20	60 mm	108 mm

Photometric data




Spectral Power Distribution Colour - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

General uniform lighting - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

Classic filament LED bulbs

Photometric data



Light Distribution Diagram - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8A19/PER/927-922/CL/G/E26/WGX 1FB T20

