



# Accessory

## CORD/modern/E27/black 1CT EU RF

This Philips cord combines a fabric wire and metal socket with matt finishing to bring a vibe to your living space. Paired with a E27 LED bulb from the Philips vintage, modern, or classic range to complete the look.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	10,950 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
Warranty period	2 years

  

Light Technical	
Luminous Efficacy (rated) (Nom)	0.00 lm/W

  

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	40 W
Lamp Current (Nom)	330 mA
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120-240 V

  

Mechanical and Housing	
Net Weight (Piece)	0.432 kg

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

  

Application Conditions	
can it be used in closed luminaires	No

  

Product Data	
Order product name	40W E27 Bulb
Full product name	CORD/modern/E27/black 1CT EU RF
Full product code	871869616776200
Order code	16776200
Material Nr. (12NC)	929001977901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696167762
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699624088