

40W E27 Bulb

929001978001



Create your perfect ambiance

This Philips cord combines a fabric wire and metal socket with matt finishing to bring a vibe to your living space. Paired with a E27 LED bulb from the Philips vintage, modern, or classic range to complete the look.

General Information

Cap-Base	E27
Nominal lifetime	10,950 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
Warranty period	2.5 years

Light Technical

Luminous Efficacy (rated) (Nom)	0.00 lm/W
---------------------------------	-----------

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	40 W
Lamp Current (Nom)	330 mA
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120-240 V

Mechanical and Housing

Net Weight (Piece)	0.432 kg
--------------------	----------

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes
Warranty	2 year(s)

Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	40W E27 Bulb
Full product name	40W E27 Bulb
Full product code	871869616777900
Order code	929001978001
Material Nr. (12NC)	929001978001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696167779
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699624101