



Specialty Lamps

8W (60W) E26 Red Bulb

LEDbulb, A19, 40 W, E26, 10950 hour(s), Plastic

LEDbulb, A19, 40 W, E26, 10950 hour(s), Plastic

Product data

General Information	
Cap-Base	E26
Nominal lifetime	10,950 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LEDbulb
Light Technical	
Beam Angle (Nom)	120 degree(s)
Color Consistency	-
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	115 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5


Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	107 mm
Overall width	60 mm
Overall height	107 mm
Dimensions (Height x Width x Depth)	107 x 60 x 107 mm
Bulb Shape	A19
Net Weight (Piece)	0.060 kg
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Specialty Lamps

Ambient temperature range	-20 to +45 °C
Application Conditions	
Wireless Technology	Not applicable
Product Data	
Order product name	8W (60W) E26 Red Bulb
Full product name	8W (60W) E26 Red Bulb



Order code	929001997805
Material Nr. (12NC)	929001997805
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463274
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463279

Dimensional drawing




Product	D	C
8W (60W) E26 Red Bulb	60 mm	107 mm

Photometric data



Light Distribution Diagram - 8A19/LED/RED/P/ND 120V 4/1FB



General uniform lighting - 8A19/LED/RED/P/ND 120V 4/1FB



Spectral Power Distribution Colour - 8A19/LED/RED/P/ND 120V 4/1FB

Specialty Lamps

Lifetime



Lumen Maintenance Diagram - 8A19/LED/RED/P/ND 120V 4/1FB

Life Expectancy Diagram

