



Specialty Lamps

8W (60W) E26 Green Bulb

LEDbulb, A19, 40 W, E26, 10950 hour(s), Plastic

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

General Information		Wattage Equivalent	
Cap-Base	E26		40 W
Nominal lifetime	10,950 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	20,000	Warm-up time to 60% light	0.5 s
Rated Lifetime (Hours)	10,950 hour(s)	Power Factor (Fraction)	0.5
Lighting Technology	LEDbulb	Voltage (Nom)	120 V
Light Technical		Temperature	
Beam Angle (Nom)	160 degree(s)	T-Case Maximum (Nom)	80 °C
Color Consistency	-	Controls and Dimming	
Color rendering index (CRI)	-	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Mechanical and Housing	
Operating and Electrical		Bulb Finish	Frosted
Line Frequency	60 Hz	Bulb Material	Plastic
Input Frequency	60 Hz	Overall length	107 mm
Power Consumption	8 W	Overall width	60 mm
Lamp Current (Nom)	115 mA	Overall height	107 mm

Specialty Lamps

Dimensions (Height x Width x Depth)	107 x 60 x 107 mm
Bulb Shape	A19
Net Weight (Piece)	0.060 kg

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	8W (60W) E26 Green Bulb
Full product name	8W (60W) E26 Green Bulb
Order code	929001997905
Material Nr. (12NC)	929001997905
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463281
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463286

Dimensional drawing



Product	D	C
8W (60W) E26 Green Bulb	60 mm	107 mm

Photometric data




General uniform lighting - 8A19/LED/GREEN/P/ND 120V 4/1FB

Light Distribution Diagram - 8A19/LED/GREEN/P/ND 120V 4/1FB


Specialty Lamps

Photometric data




Spectral Power Distribution Colour - 8A19/LED/GREEN/P/ND 120V 4/1FB

Lifetime



Lumen Maintenance Diagram - 8A19/LED/GREEN/P/ND 120V 4/1FB



Life Expectancy Diagram

