



# LED Party Bulbs

## 8A19/LED/RED/ND 120V E27 6/1FB

LEDbulb, A19, E27, 10000 hour(s)

Philips A shape party lamps provided a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays.

### Product data



General Information	
Cap-Base	E27
Nominal lifetime	10,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Warranty period	1 years
Light Technical	
Beam Angle (Nom)	120 degree(s)
Color Consistency	-
Color rendering index (CRI)	54
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	115 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5

Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	A19
Net Weight (Piece)	0.030 kg
Approval and Application	
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C
Application Conditions	
Wireless Technology	Not applicable
Product Data	
Order product name	8A19/LED/RED/ND 120V E27 6/1FB
Full product name	8A19/LED/RED/ND 120V E27 6/1FB



# LED Party Bulbs

## Lifetime



Lumen Maintenance Diagram - 8A19/LED/RED/ND 120V E27 6/1FB

Life Expectancy Diagram

