



LED Lamps

LEDBulb 19W E27 3000K 230VA80 1CT/6APR

CorePro, LEDbulb, A80, 155 W, E27, 3000 K, 2150 lm, CRI 80, 15000 hour(s), Plastic

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	12,000 hour(s)
Lighting Technology	LEDBulb
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	2,150 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	113 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471 RG1	

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	19 W
Lamp Current (Nom)	170 mA
Wattage Equivalent	155 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic

LED Lamps

Overall length	155 mm
Overall width	80 mm
Overall height	155 mm
Dimensions (Height x Width x Depth)	155 x 80 x 155 mm
Bulb Shape	A80
Net Weight (Piece)	0.147 kg

Approval and Application

Energy Consumption kWh/1000 h	19 kWh
EU RoHS compliant	Yes
EyeComfort	No
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data


Order product name	LEDBulb 19W E27 3000K 230VA80 1CT/6APR
Full product name	LEDBulb 19W E27 3000K 230VA80 1CT/6APR
Full product code	871869964051400
Order code	929002004049
Material Nr. (12NC)	929002004049
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699640514
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699640521

Dimensional drawing




Product	D	C
LEDBulb 19W E27 3000K 230VA80 1CT/6APR	80 mm	155 mm

Photometric data



Spectral Power Distribution Colour - LEDBulb 19W E27 3000K 230VA80 1CT/6APR



Light Distribution Diagram - LEDBulb 19W E27 3000K 230VA80 1CT/6APR

