



中国国家强制性产品认证证书

证书编号: 2016011002890677

发证日期: 2022年12月16日

有效期至: 2026年06月09日

认证委托人名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

产品生产者名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称
及生产地址



产品名称和系列、规格、型号 LED 模块用交流电子控制装置 (LED 控制装置, 内装式, 恒流模式, 安全特低电压, tc:85°C, ta:55°C, 控制端口调光, 定温热保护: 120°C)
见附件。220-240V ~ 50/60Hz

产品标准和技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书, 证书首次颁发日期: 2016年08月10日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2016011002890677

Valid from: Dec.16,2022

Valid until: Jun.09,2026

NAME AND REGISTERED ADDRESS OF THE APPLICANT

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

NAME AND LOCATION OF THE FACTORY



PRODUCT MODEL(S)

A.C. Supplied Electronic Controlgear For LED Modules (LED Controlgear, Built-in, Constant Current Mode, SELV, tc:85°C, ta: 55°C, Controlled Port Dimming, Temperature Declared Thermally Protected: 120°C)
See Appendix. 220-240V~ 50/60Hz

STANDARDS AND TECHNICAL REQUIREMENTS

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Aug.10,2016

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号: 2016011002890677

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3158120

型号	输出电流	最大输出电压	输出电压	输出功率
Xi LP 22W 0.3-1.0A S1 230V C123 sXt	0.3-1.05A	Max.50VDC	8-32VDC	22W
Xi LP 40W 0.3-1.0A S1 230V C123 sXt	0.3-1.05A	Max.60VDC	20-54VDC	40W
Xi LP 40W 0.2-0.7A S1 230V C123 sXt	0.2-0.7A	Max.100VDC	25-77VDC	40W
Xi LP 22W 0.2-0.7A S1 230V C123 sXt	0.2-0.7A	Max.70VDC	16-48VDC	22W

输入: 220-240V ~ 50/60Hz



中国质量认证中心

