



中国国家强制性产品认证证书

证书编号: 2019011002191932

发证日期: 2022年08月22日

有效期至: 2024年06月04日

认证委托人名称
及注册地址 昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

产品生产者名称
及注册地址 昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、
规格、型号 LED 模块用交流电子控制装置(LED 控制装置, 内装式, 自耦式, 恒流模式, ta: 50°C, tc: 75°C/80°C,
不可调光, 定温热保护: 110°C)
见附件, 220-240V~ 50/60Hz

产品标准和
技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书, 证书首次颁发日期: 2019年06月04日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019011002191932

Valid from: Aug.22,2022

Valid until: Jun.04,2024

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

PRODUCT MODEL(S)

A.C. Supplied Electronic Controlgear For LED Modules (Built-in, Auto-wound Controlgear, Constant
Current Mode, ta:50°C, tc:75°C/80°C, Non-Dimmable, Temperature Declared Thermally Protected:
110°C)
See Appendix. 220-240V ~ 50/60Hz

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Jun.04,2019

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

附 录

第 1 页 共 1 页

证书编号: 2019011002191932

纸 号: 3074788

型号	输出电压 (Vdc)	最大输出电 压 (Vdc)	输出电流 (A)	输出功 率 (W)	tc
CertaDrive 30W 350mA 85V 230V	50-85Vdc	300Vdc	0.35A	30W	75
CertaDrive 40W 350mA 115V 230V	70-115Vdc	300Vdc	0.35A	40W	75
CertaDrive 60W 350mA 170V 230V	105-170Vdc	300Vdc	0.35A	60W	80

输入均为: 220-240V~ 50/60Hz

注: 此附录与证书同时使用时有效。



中国质量认证中心

