Australia and New Zealand Certificate of Suitability- addendum

Certificate
ULL-104232-A1

Issue date
2026-06-10

Expiration date
2030-11-25

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic controlgear for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Amarjit Singh (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability-addendum

Certificate No: ULL-104232-A1
Original Date of Certification: 2025-11-25
Date of Issue/Revision: 2026-06-10

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Ratings:

Xitanium 35W 0.08-0.35A 220V S16 230V:
Un: 220-240 V, In: 0.17 A, Pn: 39 W, fn: 50/60 Hz, DC, PF: 0.9C,
Uoutput: 50-220 Vdc, Uout: 250 Vmax, Prated: 35 W,
Irated: 0.8-0.35 Adc, ta: -25…+50°C, tc: 75°C, Built-in.

Xitanium 60W 0.08-0.35A 300V S16 230V:
Un: 220-240 V, In: 0.3 A, Pn: 66 W, fn: 50/60 Hz, DC, PF: 0.9C,
Uoutput: 100-300 Vdc, Uout: 330 Vmax, Prated: 60 W,
Irated: 0.08-0.35 Adc, ta: -25…+50°C, tc: 75°C, Built-in.

Xitanium 60W 0.15-0.5A 220V S16 230V:
Un: 220-240 V, In: 0.3 A, Pn: 66 W, fn: 50/60 Hz, DC, PF: 0.9C,
Uoutput: 50-220 Vdc, Uout: 250 Vmax, Prated: 60 W,
Irated: 0.15-0.5 Adc, ta: -25…+50°C, tc: 75°C, Built-in.

Details of addendum :

Trade names “XITANIUM”, and “ADVANCE” added.

© 2026 UL LLC. All rights reserved.
Form-ULID-013925-CoS - ver 2.0