



中国国家强制性产品认证证书

证书编号: 2020011002301879

发证日期: 2022年09月08日

有效期至: 2025年06月16日

认证委托人名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

产品生产者名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED 模块用交直流电子控制装置 (LED 控制装置, 内装式, 自耦式, 恒流模式, 控制端口调光, ta: 55°C, 定温热保护: 130°C)
见附件。220-240V~ 50/60Hz; 186-250Vdc

产品标准和技术要求 GB 17625.1-2012; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2020年06月16日

经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020011002301879

Valid from: Sep.08,2022

Valid until: Jun.16,2025

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND LOCATION
OF THE FACTORY**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Built-in, Auto-wound Controlgear,
Constant Current Mode, Controlled Port Dimming, ta:55°C, Temperature Declared Thermally
Protected:130°C)
See Appendix.220-240V~ 50/60Hz ; 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Jun.16,2020

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

附 录

第 1 页 共 1 页

证书编号: 2020011002301879

纸 号: 3055239

序号	型号	输出电流	输出电压	最大输出 电压	输出功率	tc 值
1	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	0.2-0.7A	90-283Vdc	350Vdc	150W	85°C
2	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	0.3-1.05A	70-214Vdc	260Vdc	150W	85°C
3	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	0.2-0.7A	50-150Vdc	200Vdc	75W	80°C
4	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	0.3-1.05A	35-108Vdc	150Vdc	75W	80°C

输入: 220-240V~ 50/60Hz; 186-250Vdc

注: 此附录与证书同时使用时有效。



中国质量认证中心

