Australia and New Zealand Certificate of Suitability

Certificate
ULL-104546

Issue date
2026-06-16

Expiration date
2031-06-16

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic control gear for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104546
Date of Issue/Revision: 2026-06-16

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Rating:
Xi FP 22W 0.2-0.7A SNLDAE 230V S175 sXt:
Uin: 220-240 Vac, Iin: 0.12-0.11 Aac,
Uin: 186-250 Vdc, Iin: 0.09-0.006 Adc,
Pin: 26 W, fn: 50/60 Hz or DC, PF: 0.95,
Irated: 200-700 mA, Prated: 22 W,
Uoutput: 16-48 Vdc. Uout: 70 Vdc max,
ta: -40…+55 °C, tc: 85 °C, Built-in, SELV.

Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt:
Uin: 220-240 Vac, Iin: 0.12-0.11 Aac,
Uin: 186-250 Vdc, Iin: 0.09-0.006 Adc,
Pin: 26 W, fn: 50/60 Hz or DC, PF: 0.95,
Irated: 300-1050 mA, Prated: 22 W,
Uoutput: 8-32 Vdc. Uout: 50 Vdc max,
ta: -40…+55 °C, tc: 85 °C, Built-in, SELV.

Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt:
Uin: 220-240 Vac, Iin: 0.21-0.19 Aac,
Uin: 186-250 Vdc, Iin: 0.15-0.01 Adc,
Pin: 46 W, fn: 50/60 Hz or DC, PF: 0.95,
Irated: 200-700 mA, Prated: 40 W,
Uoutput: 25-77 Vdc. Uout:100 Vdc max,
ta: -40…+55 °C, tc: 85 °C, Built-in, SELV.

Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt:
Uin: 220-240 Vac, Iin: 0.21-0.19 Aac,
Uin: 186-250 Vdc, Iin: 0.15-0.01 Adc,
Pin: 46 W, fn: 50/60 Hz or DC, PF: 0.95,
Irated: 300-1050 mA, Prated: 40 W,
Uoutput: 20-54 Vdc. Uout: 60 Vdc max,
ta: -40…+55 °C, tc: 90 °C, Built-in, SELV.

© 2026 UL LLC. All rights reserved.