



中国国家强制性产品认证证书

证书编号: 2020011002272575

发证日期: 2022 年 09 月 15 日

有效期至: 2025 年 01 月 19 日

认证委托人名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

产品生产者名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED 模块用交直流电子控制装置 (LED 控制装置, 内装式, 恒流模式, 安全特低电压, 控制端口调光, ta:55°C, tc:85°C/90°C, 定温热保护: 120°C)
见附件。220-240V ~ 50/60Hz; 186-250Vdc

产品标准和技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
本证书为变更证书, 证书首次颁发日期: 2020 年 01 月 19 日
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2020011002272575

Valid from: Sep.15,2022

Valid until: Jan.19,2025

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND LOCATION
OF THE FACTORY**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Driver, Built-in, Constant Current Mode, SELV, Controlled Port Dimming, ta:55°C, tc:85°C/90°C, Temperature Declared Thermally Protected: 120°C)
See Appendix.220-240V ~ 50/60Hz; 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Jan.19,2020

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号 2020011002272575

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3050227

序号	型号	输入规格	输出电流	输出电压	最大输出电压	输出功率	tc值
1	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	220-240V~, 50/60Hz, 0.21A-0.19A	300mA-1050mA	20-54Vdc	Max. 60Vdc	40W	90℃
		186-250Vdc, 0.15-0.01A					
2	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	220-240V~, 50/60Hz, 0.21A-0.19A	200mA-700mA	25-77Vdc	Max. 100Vdc	40W	85℃
		186-250Vdc, 0.15-0.01A					
3	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	220-240V~, 50/60Hz, 0.12A-0.11A	300mA-1050mA	8-32Vdc	Max. 50Vdc	22W	85℃
		186-250Vdc, 0.09-0.006A					
4	Xi FP 22W 0.2-0.7A SNLDAE 230V S175 sXt	220-240V~, 50/60Hz, 0.12A-0.11A	200mA-700mA	16-48Vdc	Max. 70Vdc	22W	85℃
		186-250Vdc, 0.09-0.006A					

备注: 输入功率均大于 25W。



中国质量认证中心

