



中国国家强制性产品认证证书

证书编号: 2022011002517350

发证日期: 2022 年 12 月 28 日

有效期至: 2027 年 12 月 27 日

认证委托人名称 昕诺飞 (中国) 投资有限公司
及注册地址 上海市闵行区田林路 888 弄 9 号楼

产品生产者名称 昕诺飞 (中国) 投资有限公司
及注册地址 上海市闵行区田林路 888 弄 9 号楼

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED 模块用交直流电子控制装置 (LED 控制装置, 内装式, 恒流模式, 安全特低电压, 控制端口调光, ta:55°C, tc:85°C/90°C, 定温热保护: 120°C)
见附件; 220-240V~, 50/60Hz; 186-250Vdc

产品标准和技术要求 GB 17625.1-2012; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2022011002517350

Valid from: Dec.28,2022

Valid until: Dec.27,2027

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Driver, Built-in, Constant Current Mode, SELV, Controlled Port Dimming, ta:55°C, tc:85°C/90°C, Temperature Declared Thermally Protected : 120°C)
See Appendix. 220-240V ~ , 50/60Hz ; 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

证书编号：2022011002517350

第 1 页 共 1 页

本证书及附件应同时使用，信息查验说明见证书页

纸号：

序号	型号	输入规格	输出电流	输出电压	最大输出电压	输出功率	tc 值
1	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	220-240V ~ , 50/60Hz , 0.21A-0.19A 186-250Vdc , 0.15-0.01A	300mA-1050mA	20-54Vdc	Max.60Vdc	40W	90°C
2	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	220-240V ~ , 50/60Hz , 0.21A-0.19A 186-250Vdc , 0.15-0.01A	200mA-700mA	25-77Vdc	Max.100Vdc	40W	85°C
3	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	220-240V ~ , 50/60Hz , 0.12A-0.11A 186-250Vdc , 0.09-0.006A	300mA-1050mA	8-32Vdc	Max.50Vdc	22W	85°C

备注：输入功率均大于 25W。



中国质量认证中心