

External Slim Downlight DL252

DL252 G2 R SQ LED 1300 65K 18W 8" WV 1pk

External Slim Downlight DL252, 18 W, 1300 lm, 6500 K, Wide beam, White

A complete family delivering superior light with great uniformity and safety. Choose the best fit for every projects, from multiple lumen packs/wattages, and enjoy great reliable performance free of maintenance.

Product data

General Information		Luminaire light beam spread	
Light source replaceable	No		110°
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	110 to 240 V
Nominal lifetime	25,000 hour(s)	Line Frequency	50 or 60 Hz
Switching Cycle	12,500	Input Frequency	50 or 60 Hz
Lighting Technology	LED	Inrush current	44 A
Value ladder	Value	Inrush time	0.13 ms
Warranty period	1 years	Power Consumption	18 W
Light Technical		Power Factor (Fraction)	0.5
Luminous Flux	1,300 lm	Connection	Connection unit 2-pole
Correlated Color Temperature (Nom)	6500 K	Cable	Cable 0.2 m without plug
Luminous Efficacy (rated) (Nom)	72.00 lm/W	Number of products on MCB of 16 A type B	34
Color rendering index (CRI)	80	Suitable for random switching	No
Light source color	865 cool daylight	Protection class IEC	Safety class II
Optic type	Wide beam	Controls and Dimming	
		Dimmable	No

External Slim Downlight DL252

Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No


Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	Polystyrene
Optical cover material	Polypropylene
Fixation material	Steel
Housing Color	White
Optical cover finish	Matte
Overall length	220 mm
Overall width	220 mm
Overall height	20 mm
Overall diameter	220 mm
Dimensions (Height x Width x Depth)	20 x 220 x 220 mm
Net weight	0.388 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK01 [0.15 J]
Net Weight (Piece)	0.400 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Warranty	2 year(s)

Dimensional drawing



EyeComfort	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+10%/-15%
Initial chromaticity	(0.313, 0.337) <6
Power consumption tolerance	+10%/-20%

Over Time Performance (IEC Compliant)



Driver failure rate at 5000 h	0.05 %
Median useful life L70B50	25,000 hour(s)

Product Data

Order product name	DL252 G2 R SQ LED 1300 65K 18W 8" WV 1pk
Full product name	DL252 G2 R SQ LED 1300 65K 18W 8" WV 1pk
Full product code	871869973426800
Order code	73426800
Material Nr. (12NC)	929002322401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699734268
Numerator - Packs per outer box	12
EAN/UPC - Case	8718699734275

External Slim Downlight DL252

Photometric data



Light Distribution Diagram - DL252 G2 R SQ LED 1300 65K 18W 8" WV 1pk

General uniform lighting - DL252 G2 R SQ LED 1300 65K 18W 8" WV 1pk

Lifetime



L70B-50 25K-LED

