



A-Shape LED

8.8A19/AMB/927/ND D2D 6/1FB T20

LEDbulb, A19, 60 W, E26, 2700 K, 800 lm, 15000 hour(s)

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Power Consumption	
Cap-Base	E26	Lamp Current (Nom)	74 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	60 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LEDbulb	Warm-up time to 60% light	0.5 s
Warranty period	1 years	Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)	95 °C
Beam Angle (Nom)	220 degree(s)		
Luminous Flux	800 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	No
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Finish	Frosted
Color Consistency	<4	Bulb Shape	A19
Color rendering index (CRI)	90	Net Weight (Piece)	0.062 kg
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		EU RoHS compliant	Yes
Line Frequency	60 Hz		
Input Frequency	60 Hz		

A-Shape LED

Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	8.8A19/AMB/927/ND D2D 6/1FB T20
Full product name	8.8A19/AMB/927/ND D2D 6/1FB T20
Full product code	871869974949100
Order code	929002333611



Material Nr. (12NC)	929002333611
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699749491
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699749507

Dimensional drawing



Product	D	C
8.8A19/AMB/927/ND D2D 6/1FB T20	61.5 mm	109.8 mm


Photometric data



©2022 Philips Lighting B.V. All rights reserved. Page 1/1

Spectral Power Distribution Colour - 8.8A19/AMB/927/ND D2D 6/1FB T20


General uniform lighting - 8.8A19/AMB/927/ND D2D 6/1FB T20



Light Distribution Diagram - 8.8A19/AMB/927/ND D2D 6/1FB T20

A-Shape LED

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 8.8A19/AMB/927/ND D2D 6/1FB T20

