



External Slim Downlight DL252

DL252 G2 R SQ LED 2000 40K 24W 11" WV

External Slim Downlight DL252, 24 W, 2000 lm, 4000 K, Beam angle 110°, White

A complete family delivering superior light with great uniformity and safety. Choose the best fit for every projects, from multiple lumen packs/wattages, and enjoy great reliable performance free of maintenance.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Nominal lifetime	25,000 hour(s)
Switching Cycle	12,500
Lighting Technology	LED
Warranty period	1 years
Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	83.00 lm/W
Color rendering index (CRI)	80
Light source color	840 neutral white
Optic type	Beam angle 110°
Luminaire light beam spread	110°

Operating and Electrical	
Input Voltage	110 to 240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Inrush current	14.9 A
Inrush time	0.5 ms
Power Consumption	24 W
Power Factor (Fraction)	0.5
Connection	Flying leads/wires
Suitable for random switching	Not applicable
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

External Slim Downlight DL252

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polystyrene
Optical cover material	Polystyrene
Fixation material	Steel
Housing Color	White
Optical cover finish	Frosted
Overall length	293 mm
Overall width	293 mm
Overall height	20 mm
Overall diameter	293 mm
Dimensions (Height x Width x Depth)	20 x 293 x 293 mm
Net weight	0.673 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.760 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Warranty	2 year(s)

EyeComfort	Yes
Ambient temperature range	-10 to +40 °C

Initial Performance (IEC Compliant)

Initial chromaticity	(0.3800 , , 0.3800) 6 SDCM
----------------------	----------------------------


Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.015 %
Median useful life L70B50	25,000 hour(s)

Product Data



Order product name	DL252 G2 R SQ LED 2000 40K 24W 11" WV
Full product name	DL252 G2 R SQ LED 2000 40K 24W 11" WV
Full product code	871869974883800
Order code	929002346401
Material Nr. (12NC)	929002346401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699748838
Numerator - Packs per outer box	12
EAN/UPC - Case	8718699748845

Dimensional drawing



External Slim Downlight DL252

Photometric data



Light Distribution Diagram - DL252 G2 R SQ LED 2000 40K 24W 11" WV

General uniform lighting - DL252 G2 R SQ LED 2000 40K 24W 11" WV

Lifetime



L70B-50 25K-LED

