



Classic filament LED bulbs

LED classic 120W A67 E27 CW CL ND 1SRT4

CorePro, LEDbulb, A67, 120 W, E27, 4000 K, 2000 lm, CRI 80, 15000 hour(s), Glass

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Color Code	840 [CCT of 4000K]
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	2,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	153.00 lm/W

Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	13 W
Lamp Current (Nom)	120 mA
Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V

Classic filament LED bulbs

Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Overall length	121 mm
Overall width	70 mm
Overall height	121 mm
Dimensions (Height x Width x Depth)	121 x 70 x 121 mm
Bulb Shape	A67
Net Weight (Piece)	0.034 kg
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	13 kWh
EPREL Registration Number	374897
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	LED classic 120W A67 E27 CW CL ND 1SRT4
Full product name	LED classic 120W A67 E27 CW CL ND 1SRT4
Full product code	871869976437100
Order code	929002371601
Material Nr. (12NC)	929002371601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699764371
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699764388



Dimensional drawing



Product	D	C
LED classic 120W A67 E27 CW CL ND 1SRT4	70 mm	121 mm


Classic filament LED bulbs

Photometric data



General uniform lighting - LED classic 120W A67 E27 CW CL ND 1SRT4

Light Distribution Diagram - LED classic 120W A67 E27 CW CL ND 1SRT4




Spectral Power Distribution Colour - LED classic 120W A67 E27 CW CL ND 1SRT4

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED classic 120W A67 E27 CW CL ND 1SRT4

Classic filament LED bulbs

