



Classic filament LED bulbs

LEDclassic 11W A60 E27 smoky ND RFSRT4

MASTER Value, LEDbulb, A60, 11 W, E27, 1800 K, 100 lm, CRI 80, 15000 hour(s), Glass

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb
Warranty period	2.5 years
Light Technical	
Color Code	818 [CCT of 1800K]
Color Code	818 [CCT of 1800K]
Luminous Flux	100 lm
Color Designation	1800
Correlated Color Temperature (Nom)	1800 K
Luminous Efficacy (rated) (Nom)	43 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	2.3 W
Lamp Current (Nom)	21 mA
Wattage Equivalent	11 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.54
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	40 °C

Classic filament LED bulbs

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	smoky
Bulb Material	Glass
Overall length	106 mm
Overall width	60 mm
Overall height	106 mm
Dimensions (Height x Width x Depth)	106 x 60 x 106 mm
Bulb Shape	A60
Net Weight (Piece)	0.028 kg

Approval and Application

Energy Consumption kWh/1000 h	3 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +40 °C


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data



Order product name	LEDclassic 11W A60 E27 smoky ND RFSRT4
Full product name	LEDclassic 11W A60 E27 smoky ND RFSRT4
Full product code	871869975963600
Order code	929002380501
Material Nr. (12NC)	929002380501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699759636
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699759643

Dimensional drawing



Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm

Photometric data




Spectral Power Distribution Colour - LEDclassic 11W A60 E27 smoky ND RFSRT4

Light Distribution Diagram - LEDclassic 11W A60 E27 smoky ND RFSRT4

Classic filament LED bulbs

Photometric data



General uniform lighting - LEDclassic 11W A60 E27 smoky ND RFSRT4

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 11W A60 E27 smoky ND RFSRT4

