



## Other LED tube

### Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T5
Net Weight (Piece)	0.191 kg


### Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C

### Product Data


Order product name	MAS Ledtube 1200mm HO 16W 840 T5 DC
Full product name	MAS Ledtube 1200mm HO 16W 840 T5 DC
Full product code	871869976523100
Order code	929002387408
Material Nr. (12NC)	929002387408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699765231
Numerator - Packs per outer box	20
EAN/UPC - Case	8718699765248

### Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS Ledtube 1200mm HO 16W 840 T5 DC	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm

### Photometric data




Light Distribution Diagram - MAS Ledtube 1200mm HO 16W 840 T5 DC



Spectral Power Distribution Colour - MAS Ledtube 1200mm HO 16W 840 T5 DC



# Other LED tube

## Photometric data




General uniform lighting - MAS Ledtube 1200mm HO 16W 840 T5 DC

## Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - MAS Ledtube 1200mm HO 16W 840 T5 DC


FailureRate



Lumen Maintenance Diagram - MAS Ledtube 1200mm HO 16W 840 T5 DC

## Other LED tube

### Lifetime



LifetimeVsTc

