



LED PAR30 S/L

LEDspot 70W PAR30S 827 100-240V 25D ND

LEDspot, PAR30S, 70 W, E27, 2700 K, 900 lm, 25000 hour(s)

LEDspot, PAR30S, 70 W, E27, 2700 K, 900 lm, 25000 hour(s), 94.00 lm/W

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Warranty period	2 years
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	900 lm
Luminous Intensity (Nom)	3,500 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	94.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	9.5 W

Lamp Current (Nom)	75 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	100-240 V

Temperature	
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	PAR30S
Net Weight (Piece)	0.285 kg

Approval and Application	
Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

LED PAR30 S/L

Application Conditions


Wireless Technology Not applicable

Product Data

Order product name	LEDspot 70W PAR30S 827 100-240V 25D ND
Full product name	LEDspot 70W PAR30S 827 100-240V 25D ND
Full product code	871869977469100
Order code	929002403212



Material Nr. (12NC)	929002403212
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699774691
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699774707

Dimensional drawing




Product	D	C
LEDspot 70W PAR30S 827 100-240V 25D ND	97 mm	97 mm

Photometric data



Spectral Power Distribution Colour - LEDspot 70W PAR30S 827 100-240V 25D ND



Accent Lighting Spots - LEDspot 70W PAR30S 827 100-240V 25D ND



Light Distribution Diagram - LEDspot 70W PAR30S 827 100-240V 25D ND

LED PAR30 S/L

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDspot 70W PAR30S 827 100-240V 25D ND

