



TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

TForce Core HB 40W E27 865 GN3

LED HPI, T-shape T120, Mains only, 220–240 V, 40 W, 65W CFL, 55W HID, E27, 6500 K, 4000 lm, 15000 hour(s)

LED HPI, T-shape T120, Mains only, 220–240 V, 40 W, LED alternative to 65W CFL, 55W HID, E27, 6500 K, 4000 lm, 15000 hour(s), 100.00 lm/W

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED HPI
Warranty period	1 years
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	4,000 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K

Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	40 W
Lamp Current (Nom)	330 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5

TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Voltage (Nom)	220-240 V
Wattage Equivalent (LED HID only)	65W CFL, 55W HID
Ballast Compatibility	Mains only
Temperature	
T-Case Maximum (Nom)	79 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T-shape T120
Net Weight (Piece)	0.164 kg
Approval and Application	
Energy Saving Product	Yes
Energy Consumption kWh/1000 h	40 kWh

EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	TForce Core HB 40W E27 865 GN3
Full product name	TForce Core HB 40W E27 865 GN3
Full product code	871869978065400
Order code	929002408608
Material Nr. (12NC)	929002408608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699780654
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699780661

Dimensional drawing




Product	D	C
TForce Core HB 40W E27 865 GN3	118 mm	193 mm

Photometric data




Spectral Power Distribution Colour - TForce Core HB 40W E27 865 GN3



Light Distribution Diagram - TForce Core HB 40W E27 865 GN3

TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Technical Parameters 43
Page 11

General uniform lighting - TForce Core HB 40W E27 865 GN3

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - TForce Core HB 40W E27 865 GN3

