



# TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

## TForce Core HB 50W E27 830 GN3

LED HPI, T-shape T140, Mains only, 50 W, 75W CFL, 70W HID, E27, 3000 K, 4800 lm, 15000 hour(s)

Philips TrueForce Core LED I&R lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce Core LED I&R lamps and bypass the existing ballast while enhancing the lighting quality.

### Product data

General Information		Operating and Electrical	
Cap-Base	E27	Luminous Flux	4,800 lm
Nominal lifetime	15,000 hour(s)	Color Designation	White (WH)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	3000 K
Lighting Technology	LED HPI	Luminous Efficacy (rated) (Nom)	96.00 lm/W
Warranty period	1 years	Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	830 [CCT of 3000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	180 degree(s)		

# TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Input Frequency	50 to 60 Hz
Power Consumption	50 W
Lamp Current (Nom)	418 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Wattage Equivalent (LED HID only)	75W CFL, 70W HID
Ballast Compatibility	Mains only

## Temperature

T-Case Maximum (Nom)	78 °C
----------------------	-------

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	T-shape T140
Net Weight (Piece)	0.150 kg


## Approval and Application

Energy Saving Product	Yes
Energy Consumption kWh/1000 h	50 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C

## Product Data


Order product name	TForce Core HB 50W E27 830 GN3
Full product name	TForce Core HB 50W E27 830 GN3
Full product code	871869978067800
Order code	929002408708
Material Nr. (12NC)	929002408708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699780678
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699780685

## Dimensional drawing




Product	D	C
TForce Core HB 50W E27 830 GN3	139 mm	221 mm

## Photometric data



Light Distribution Diagram - TForce Core HB 50W E27 830 GN3



Spectral Power Distribution Colour - TForce Core HB 50W E27 830 GN3

