



Corepro - LED HID HPL



TForce Core LED HPL 36W E27 840 FR

CorePro, LED HPL, Oval, Mains only, 36 W, HPL 125W, SON 70W, E27, 4000 K, 6000 lm, CRI 80, 25000 hour(s)

Philips TrueForce Core LED HPL lamps are an easy, LED solution with a short pay-back to replace High Intensity Discharge (HID) lamps. This new generation of LED Core Post-Top lamps brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while delivering instant saving for a low initial investment. Furthermore, TrueForce CorePro LED HPL lamps are designed to have the same lamp size and light distribution as their HID alternatives. And thanks to our high-power LED filament technology, you'll never know the difference. Plus, their unique IP65 design means that TrueForce Core LED HPL Post-Top lamps can be used for outdoor, as well as indoor applications.

Warnings and Safety

- Installation should always be performed by a qualified electrician or installer. Use the installation guide for instructions.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED HPL
Flux measurement reference	Sphere
Warranty period	3 years

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	6,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	166 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

Corepro - LED HID HPL

LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	36 W
Lamp Current (Nom)	143 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Inrush current at mains	32
Max. lamp no. on MCB B type 10A - Mains	6
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A - Mains	10
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Wattage Equivalent (LED HID only)	HPL 125W, SON 70W
Ballast Compatibility	Mains only

Temperature

T-Case Maximum (Nom)	43.3 °C
----------------------	---------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
-------------	---------

Bulb Material	Glass
Bulb Shape	Oval
Net Weight (Piece)	0.204 kg

Approval and Application

Energy Efficiency Class	C
Energy Saving Product	Yes
Energy Consumption kWh/1000 h	36 kWh
EPREL Registration Number	403655
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	-30 to +45 °C


Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data

Order product name	TForce Core LED HPL 36W E27 840 FR
Full product name	TForce Core LED HPL 36W E27 840 FR
Full product code	871951429929000
Order code	929002481302
Material Nr. (12NC)	929002481302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514299290
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514299306



Dimensional drawing



Product	D	C
TForce Core LED HPL 36W E27 840 FR	91.5 mm	249 mm

Corepro - LED HID HPL



Photometric data



General uniform lighting - TForce Core LED HPL 36W E27 840 FR


Light Distribution Diagram - TForce Core LED HPL 36W E27 840 FR

General uniform lighting - TForce Core LED HPL 36W E27 840 FR



Spectral Power Distribution Colour - TForce Core LED HPL 36W E27 840 FR



Spectral Power Distribution Colour - TForce Core LED HPL 36W E27 840 FR



Light Distribution Diagram - TForce Core LED HPL 36W E27 840 FR

Corepro - LED HID HPL

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - TForce Core LED HPL 36W E27 840 FR

