



Apex Ceiling light

Apex RT LED 40W 5700K

With its EyeComfort design, Apex provides comfortable high quality LED light for home and residential project. Its long lifetime and high lumen maintenance ensures bright light level over time. With various shapes, sizes, it enables to serve from bedroom to big living room, and dining to kitchen space. Installation becomes easier with easy connector and installation bracket.

Product data

| General Information | |
|------------------------------------|----------------|
| Light source replaceable | No |
| Lighting Technology | LED |
| Value ladder | Value |
| Warranty period | 1 years |
| Light Technical | |
| Luminous Flux | 3,400 lm |
| Correlated Color Temperature (Nom) | 5700 K |
| Luminous Efficacy (rated) (Nom) | 85.00 lm/W |
| Color rendering index (CRI) | 80 |
| Light source color | 857 daylight |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Input Frequency | 50 or 60 Hz |
| Power Consumption | 40 W |
| Power Factor (Fraction) | 0.5 |
| Protection class IEC | Safety class I |

| Controls and Dimming | |
|-------------------------------------|---|
| Dimmable | No |
| Constant light output | No |
| Mechanical and Housing | |
| Housing Material | Metal-Plastic |
| Housing Color | White |
| Overall length | 510 mm |
| Overall width | 290 mm |
| Overall height | 73 mm |
| Dimensions (Height x Width x Depth) | 73 x 290 x 510 mm |
| Ingress protection code | IP20 [Finger-protected] |
| Net Weight (Piece) | 0.940 kg |
| Approval and Application | |
| Flammability mark | For mounting on normally flammable surfaces |
| EU RoHS compliant | Yes |
| Ambient temperature range | -20 to +40 °C |
| Initial Performance (IEC Compliant) | |
| Initial chromaticity | (0.3287, 0.3425) 6 |

Apex Ceiling light

Over Time Performance (IEC Compliant)

Median useful life L70B50 20.000 hour(s)

Product Data

Order product name Apex RT LED 40W 5700K
 Full product name Apex RT LED 40W 5700K
 Full product code 871951429409700
 Order code 929002612681

Material Nr. (12NC) 929002612681


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8719514294097


Numerator - Packs per outer box 1

EAN/UPC - Case 8719514294097

Dimensional drawing



Photometric data





General Uniform Lighting - Apex RT LED 40W 5700K

General uniform lighting - Apex RT LED 40W 5700K

Apex Ceiling light

Lifetime



Lumen Maintenance Diagram - Apex RT LED 40W 5700K

L70B50 20K-LED

