



Apex Ceiling light

Apex L LED 45W 5700K

With its EyeComfort design, Apex provides comfortable high quality LED light for home and residential project. Its long lifetime and high lumen maintenance ensures bright light level over time. With various shapes, sizes, it enables to serve from bedroom to big living room, and dining to kitchen space. Installation becomes easier with easy connector and installation bracket.

Product data


General Information		Controls and Dimming	
Light source replaceable	No	Dimmable	No
Lighting Technology	LED	Constant light output	No
Value ladder	Value		
Warranty period	1 years		
Light Technical		Mechanical and Housing	
Luminous Flux	4,000 lm	Housing Material	Metal-Plastic
Correlated Color Temperature (Nom)	5700 K	Housing Color	White
Luminous Efficacy (rated) (Nom)	88.00 lm/W	Overall length	1,180 mm
Color rendering index (CRI)	80	Overall width	148 mm
Light source color	857 daylight	Overall height	70 mm
		Dimensions (Height x Width x Depth)	70 x 148 x 1180 mm
		Ingress protection code	IP20 [Finger-protected]
		Net Weight (Piece)	1.200 kg
Operating and Electrical		Approval and Application	
Input Voltage	220 to 240 V	Flammability mark	For mounting on normally flammable surfaces
Line Frequency	50 or 60 Hz	EU RoHS compliant	Yes
Input Frequency	50 or 60 Hz	Ambient temperature range	-20 to +40 °C
Power Consumption	45 W		
Power Factor (Fraction)	0.5		
Protection class IEC	Safety class I	Initial Performance (IEC Compliant)	
		Initial chromaticity	(0.3287, 0.3425) 6

Apex Ceiling light


Over Time Performance (IEC Compliant)	
Median useful life L70B50	20,000 hour(s)
Product Data	
Order product name	Apex L LED 45W 5700K
Full product name	Apex L LED 45W 5700K
Full product code	871951429411000
Order code	29411000

Material Nr. (12NC)	929002612881
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514294110
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514294110

Dimensional drawing



Photometric data




Technical Drawings 1:11 Photo Lighting 1:11 Page 117


General uniform lighting - Apex L LED 45W 5700K

Apex Ceiling light

Lifetime



Lumen Maintenance Diagram - Apex L LED 45W 5700K



L70B50 20K-LED

