



# Apex Ceiling light

## Apex L LED 45W 5700K

With its EyeComfort design, Apex provides comfortable high quality LED light for home and residential project. Its long lifetime and high lumen maintenance ensures bright light level over time. With various shapes, sizes, it enables to serve from bedroom to big living room, and dining to kitchen space. Installation becomes easier with easy connector and installation bracket.

### Product data

General Information	
Light source replaceable	No
Lighting Technology	LED
Value ladder	Value
Warranty period	1 years

Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	88.00 lm/W
Color rendering index (CRI)	80
Light source color	857 daylight

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	45 W
Power Factor (Fraction)	0.5
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No
Constant light output	No

Mechanical and Housing	
Housing Material	Metal-Plastic
Housing Color	White
Overall length	1,180 mm
Overall width	148 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 148 x 1180 mm
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	1.200 kg

Approval and Application	
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Initial chromaticity	(0.3287, 0.3425) 6

# Apex Ceiling light

## Over Time Performance (IEC Compliant)

Median useful life L70B50 20,000 hour(s)

## Product Data

Order product name Apex L LED 45W 5700K  
 Full product name Apex L LED 45W 5700K  
 Full product code 871951429411000  
 Order code 929002612881

Material Nr. (12NC) 929002612881


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8719514294110


Numerator - Packs per outer box 1

EAN/UPC - Case 8719514294110

## Dimensional drawing



## Photometric data





Technical Parameters 1.1.1 | Apex Lighting BV | Page 11

## General uniform lighting - Apex L LED 45W 5700K

# Apex Ceiling light

## Lifetime



Lumen Maintenance Diagram - Apex L LED 45W 5700K

L70B50 20K-LED

