



# External Slim Downlight DL252

## DL252 G2 SF SQ LED 2000 40K 24W 11" WV

External Slim Downlight DL252, 24 W, 2000 lm, 4000 K, Wide beam, White

Metal, White, Power supply unit (On/Off), 2000 lm, 24 W, 83.00 lm/W, 4000 K, (0.380, 0.380) <6, Wide beam, Matte, Polypropylene, IP20 | Finger-protected, IK01 | 0.15 J, Safety class II, Connection unit 2-pole

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Nominal lifetime	25,000 hour(s)
Switching Cycle	12,500
Lighting Technology	LED
Warranty period	1 years

Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	83.00 lm/W
Color rendering index (CRI)	80
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	110°

Operating and Electrical	
Input Voltage	110 to 240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Inrush current	55 A
Inrush time	0.1 ms
Power Consumption	24 W
Power Factor (Fraction)	0.5
Connection	Connection unit 2-pole
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A type B 28	
Suitable for random switching	No
Protection class IEC	Safety class II


Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)

## External Slim Downlight DL252

Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Metal
Reflector material	-
Optic material	Polystyrene
Optical cover material	Polypropylene
Fixation material	Steel
Housing Color	White
Optical cover finish	Matte
Overall length	285 mm
Overall width	285 mm
Overall height	28 mm
Overall diameter	285 mm
Dimensions (Height x Width x Depth)	28 x 285 x 285 mm
Net weight	0.725 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK01 [0.15 J]
Net Weight (Piece)	0.725 kg
<b>Approval and Application</b>	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes



Warranty	2 year(s)
EyeComfort	Yes
Ambient temperature range	-20 to +40 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+10%/-15%
Initial chromaticity	(0.380, 0.380) <6
Power consumption tolerance	+10%/-20%
<b>Over Time Performance (IEC Compliant)</b>	
Driver failure rate at 5000 h	0.05 %
Median useful life L70B50	25,000 hour(s)
<b>Product Data</b>	
Order product name	DL252 G2 SF SQ LED 2000 40K 24W 11" WV
Full product name	DL252 G2 SF SQ LED 2000 40K 24W 11" WV
Full product code	871869974919400
Order code	929002636501
Material Nr. (12NC)	929002636501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699749194
Numerator - Packs per outer box	12
EAN/UPC - Case	8718699749200

### Dimensional drawing



# External Slim Downlight DL252

## Photometric data



General uniform lighting - DL252 G2 SF SQ LED 2000 40K 24W 11" WV

Light Distribution Diagram - DL252 G2 SF SQ LED 2000 40K 24W 11" WV

