



Corepro LED Strip

LS155 LED12 12W 840 5M 24V LA

A complete family that are bright, slim, safe & reliable. Choose the best fit for every projects, from 4 lumen packs/wattages, and 4 CCTs, and enjoy easy installation with slimness

Product data

General Information	
Driver included	No
Switching Cycle	15,000
Warranty period	1 years
Light Technical	
Luminous Flux	1,250 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	80
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Voltage	24 V
Initial CLO power consumption	- W
Power Consumption	54 W
Protection class IEC	Safety class III
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Metal-Plastic
Overall length	5,000 mm
Overall width	8 mm
Overall height	1.4 mm
Dimensions (Height x Width x Depth)	1 x 8 x 5000 mm
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	0.060 kg
Approval and Application	
Glow-wire test	-
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Ambient temperature range	-10 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.3771, 0.3772) 3.5SDCM
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	20,000 hour(s)

Corepro LED Strip

Product Data

Order product name	LS155 LED12 12W 840 5M 24V LA
Full product name	LS155 LED12 12W 840 5M 24V LA
Full product code	872016925670500
Order code	929002650912
Material Nr. (12NC)	929002650912

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169256705
Numerator - Packs per outer box	40
EAN/UPC - Case	8720169256729

Dimensional drawing

