



Essential SmartBright LED Downlight

DN500B G3 LED6/CW 6W 220V D90 RD

Essential SmartBright LED Downlight, 6 W, 600 lm, 6500 K, Beam angle 110°, White

Essential SmartBright G2 LED Downlight is value for money product with high efficacy, good quality and reliability. It offers multiple configurations from 300lm to 2000lm output, to replace conventional downlight. It can be used for shopping mall, retail store, residential and office. It's an ideal product family to distribute in trade market.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Lighting Technology	LED
Warranty period	3 years

Light Technical	
Luminous Flux	600 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color rendering index (CRI)	80
Light source color	865 cool daylight
Optic type	Beam angle 110°
Luminaire light beam spread	110°

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Inrush current	2.03 A
Inrush time	0.12 ms
Power Consumption	6 W
Power Factor (Fraction)	0.9
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A type B	167
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)

Essential SmartBright LED Downlight

Constant light output	No
-----------------------	----

Mechanical and Housing

Housing Material	Metal-Plastic
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Matte
Overall length	115 mm
Overall width	115 mm
Overall height	40 mm
Overall diameter	115 mm
Dimensions (Height x Width x Depth)	40 x 115 x 115 mm
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.100 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(IEC6500K, 0.313, 0.337) < 5SDCM
Power consumption tolerance	+/-10%


Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.012 %
Median useful life L70B50	30,000 hour(s)

Product Data



Order product name	DN500B G3 LED6/CW 6W 220V D90 RD
Full product name	DN500B G3 LED6/CW 6W 220V D90 RD
Full product code	692234193551000
Order code	929002677140
Material Nr. (12NC)	929002677140
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341935510
Numerator - Packs per outer box	24
EAN/UPC - Case	6922341935527

Dimensional drawing



Essential SmartBright LED Downlight

Photometric data



General uniform lighting - DN500B G3 LED6/CW 6W 220V D90 RD

Light Distribution Diagram - DN500B G3 LED6/CW 6W 220V D90 RD

